

# 台式离心机 H-36 $\alpha$

离心状态可见




12大类丰富转子可选


可订制特殊样式  
可订制适配器

本体仕様	H-36 $\alpha$
最高转速	6,000[rpm] (RA-321)
最大离心力	5,070[ $\times g$ ] (RA-321)
最大容量	1,080[ml] (RF-126、PB-126)
转速控制	数字显示 10[rpm]~6,000[rpm] (10/100rpm单位)
离心力控制	数字显示 10[ $\times g$ ]~6,000[ $\times g$ ] (10/100 $\times g$ 单位)
时间	数字显示 1~999[ $\mu$ min] (1/10[ $\mu$ min] 为单位设置) 数字显示 1~999[ $\mu$ sec] (1/10[ $\mu$ sec] 为单位设置)
$\times g \cdot \text{sec}$ 模式	(1.00~9.99) $\times 10^9$ [ $\times g \cdot \text{sec}$ ]
记忆模式	10个 (转速、离心力、时间、加速、减速)
加速	3种
减速	3种 + 自然减速
梯度密度离心	3种
密度离心	1种
运转提示	停止、运转中、LED显示 (红、黄、绿色显示不同状态)
转子寿命提示	时间显示器显示
电源	单相100[V] 10[A]
尺寸	450 $\times$ 530 $\times$ 376[mm]
重量	42[kg]

梯度离心模式



密度离心模式



# 转子参数

转子	吊篮—树脂箱	容量(ml)×离心管个数(尺寸)	转子半径	最高转速及离心力	
RF-110	4-Place Rotor				
	PA-110	10×48 (φ13×110)	15.9	3500rpm 2181×g	
	PB-110	15×32 (φ16.5×105)	15.4	3500rpm 2110×g	
	MC-110	50×4 (φ35×100)	16.5	5000rpm 4620×g	
	PO-110	Culturbe Tube15×16	16.8	3500rpm 2300×g	
	ME-110	50×8 (φ35×100)	16.5	3500rpm 2260×g	
	MF-110	100×4 (φ45×120)	16.0	4000rpm 2860×g	
	PG-110	Pyrex 14×16 (φ16×125)	16.7	3500rpm 2290×g	
	MES-110	Culture Tube 50×8 (ADS-012)	16.5	4100rpm 3100×g	
	ADS-012	Culture Tube Admpter for Mycobacterlum with sealed cap			
RF-120	4-Place Rotor				
	MT-100	PA-120-PF-120 for MT-100			
		PA-120	10×72 (φ13×110)	15.7	3500rpm 2150×g
		PB-120	15×40 (φ16.5×105)		
		PC-120	50×8 (φ35×100)		
		PD-120	Culture Tube 15×24		
		PE-120	Culture Tube 50×8		
		PF-120	RIA×84 (φ12×75)		
	MG-120	100×4 (φ45×120)	17		
RF-121	4-Place Rotor				
	MT-104	PA-121-PN-121 for MT-104			
		PA-121	10×84 (φ13×110)	16.4	3500rpm 2250×g
		PB-121	15×48 (φ16.5×105)		
		PC-121	50×16 (φ35×100)		
		PD-121	Culture Tute 15×28		
		PE-121	Culture Tute 50×16		
		PF-121	RIA×100 (φ12×75)		
		PG-121	Nalgere 250×4		
		PM-121	100×4 (φ45×120)		
		PN-121	15×60 (φ16.5×105)	16.1	3000rpm 1620×g
	MT-106	PH-121-PL-121 for MT-108 with Sealing Cap			
		PH-121	10×16 (φ13×110)	17.0	3500rpm 2330×g
		PI-121	15×40 (φ16.5×105)		
		PJ-121	50×8 (φ35×100)		
		PK-121	Culture Tute 15×16		
		PL-121	Culture Tute 50×8		
RF-126	4-Place Rotor				
	MT-109	PA-126-PM-126 for MT-109			
		PA-126	10×100 (φ13×110)	16.4	3500rpm 2250×g
		PB-126	15×72 (φ16.5×105)		
		PC-126	50×16 (φ35×100)		
		PD-126	Culture Tute 15×36		
		PE-126	Culture Tute 50×16		
		PF-126	RIA×120 (φ12×75)		
		PG-126	Nalgene 250×4		
		PM-126	100×4 (φ45×120)		
RF-122A		120孔板转子×8	13.4	2000rpm 600×g	
RF-123A		96孔板转子×4	13.4	2000rpm 600×g	
RF-124T		96孔深孔板×2	13.2	3200rpm 1510×g	
RF-300A		含适量水分的转子	9.9	3000rpm 1000×g	
RF-200A		角转子15×24 (φ16.5×105)	16.3	3500rpm 2230×g	
RA-310A		角转子15×26 (φ16×114)	13	5000rpm 3630×g	
RA-321		角转子50×8	12.6	6000rpm 5070×g	
RA-501		角转子1.5 (2.2)×12	6.4	6000rpm 2600×g	



MES-110



RF-126



RF-122A



RF-124T



RF-300A



RA-310A



RA-501